




# Large-sized, High-homogeneity Synthetic Silica Glass

Currently offering standard sizes up to  $\phi 800 \times t 55$  mm

Please feel free to contact our sales office for further details on larger sizes, as well as polished and coated products.


## High transmittance

Suitable to  
VUV - NIR




## High homogeneity

$\leq 2$  ppm  
 $\phi 600 \times t 100$  mm



## Low birefringence

$\leq 0.5$  nm/cm  
 $\phi 600 \times t 100$  mm



Each measurement data shown as representative value.