



# XC65Dx(-LS)

Digital Cross Scanners



The ultimate scanner  
for feature measurement and more

# FEATURES AND BENEFITS



## BENEFITS

- Full 3D capture of complex surfaces and features geometry in a single scan
- Scans any material without spraying
- Faster feature inspection by eliminating scanner re-orientation
- Easy macro-based part programming accelerates measurement preparation
- Seamless retrofit with most leading CMM brands

## KEY FEATURES

- Patented multi-stripe laser technology observes part from 3 directions
- High-speed digital technology boosts scanning frequency
- Unique point-per-point laser intensity adaptation
- Non-contact laser scanning is ideal to measure flexible or fragile parts
- XC65Dx-LS long stand-off variant for optimum capture into deep pockets and slots

## APPLICATIONS

- Sheet metal vehicle body parts
- Driveline casting inspection (engine castings, etc.)
- Plastic molding and blow molding (composite fuel tanks, plastic body parts, etc.)
- Inspection of 2D and complex 3D features
- Gap and flush of door/fender splines

## TECHNICAL SPECIFICATIONS

	XC65Dx	XC65Dx-LS
Scan speed	Cross Scanner mode: 3 x 25,000 pts/s Line scanner mode: 1 x 75,000 pts/s 75 lines/s	
Width of view	3x65 mm (3x2.56")	3x65 mm (3x2.56")
Depth of view	3x65 mm (3x2.56")	3x65 mm (3x2.56")
Stand-off distance	75 mm (2.95")	170 mm (6.69")
Multi-stylus test (MPE <sub>AL</sub> ) <sup>1</sup>	9 µm (0.00035")	9 µm (0.00035")
ISO Probing form error <sup>2</sup>	25 µm (0.00098")	35 µm (0.00138")
Dimensions	155x86x142 mm (6.1x3.4x5.6")	155x86x142 mm (6.1x3.4x5.6")
Weight (approx.)	440 g (0.97 lbs)	480 g (1.06 lbs)
CMM mounting	Renishaw PH10M(Q) motorized indexing probe head with Multiwire	
Laser class	2 (Visible)	

<sup>1</sup> Comparable to EN/ISO10360-5, for a CMM with accuracy of 2µm + L/350 or better

<sup>2</sup> ISO 10360-8:2013: P<sub>form,Sph,1x25,TI,ODS,MPE</sub> - "Maximum probing form error" using 25 representative points in translatory scanning mode

For a complete list of specifications, please request the datasheet.

**CLASS 2 LASER PRODUCT**  
 Max output = 4.0 & 1 mW (XC65Dx)  
 Max output = 5.6 & 1 mW (XC65Dx-LS)  
 660 & 635nm  
 IEC 60825-1 Edition 2.0 2007-03



### NIKON METROLOGY NV

Geldenaaksebaan 329  
 B-3001 Leuven, Belgium  
 phone: +32 16 74 01 00 fax: +32 16 74 01 03  
 Sales.NM@nikon.com

NIKON METROLOGY EUROPE NV  
 tel. +32 16 74 01 01  
 Sales.Europe.NM@nikon.com

NIKON METROLOGY GMBH  
 tel. +49 6023 91733-0  
 Sales.Germany.NM@nikon.com

NIKON METROLOGY SARL  
 tel. +33 1 60 86 09 76  
 Sales.France.NM@nikon.com

NIKON METROLOGY, INC.  
 tel. +1 810 2204360  
 Sales.US.NM@nikon.com

NIKON METROLOGY UK LTD.  
 tel. +44 1332 811349  
 Sales.UK.NM@nikon.com

### NIKON CORPORATION

Shinagawa Intercity Tower C, 2-15-3, Konan,  
 Minato-ku, Tokyo 108-6290 Japan  
 Telefon: +81-3-6433-3701 Fax: +81-3-6433-3784  
 www.nikon.com/products/industrial-metrology/

NIKON INSTRUMENTS (SHANGHAI) CO. LTD.  
 Tel.: +86 21 5836 0050  
 Tel.: +86 10 5869 2255 (Beijing office)  
 Tel.: +86 20 3882 0550 (Guangzhou office)

NIKON SINGAPORE PTE. LTD.  
 Tel.: +65 6559 3618  
 nsg.industrial-sales@nikon.com

NIKON MALAYSIA SDN. BHD.  
 Tel.: +60 3 7809 3609

NIKON INSTRUMENTS KOREA CO. LTD.  
 Tel.: +82 2 2186 8400

